


# 2D MACRO-PROFILE COMPUTERIZED STAND


MICROTECH



CUSTOM RANGE FOR REQUEST

Item No	Axis	Range		Resolution		Accuracy		Weight	Preset	Go/NoGo	Max/Min	Formula	Timer	Temp comp	Linear corr	Calibr date	Recharge	Memory	WIRELESS	USB	Display
		X	Z	X	Z	X	Z														
		mm	mm	mm	mm	mm	mm														
27720902	1D	0-900	0-12					7.0	•	•	•	•	•	•	•	•	•				
27720900	2D			0,01		±0,030	±0,002	7.2	•	•	•	•	•	•	•	•	•				
27721802	1D	0-1800	0-12					11.5	•	•	•	•	•	•	•	•	•				
27721800	2D			0,01		±0,060		11.7	•	•	•	•	•	•	•	•	•				
27722802	1D	0-2800	0-25		0.0001			20.5	•	•	•	•	•	•	•	•	•				
27722800	2D			0,01		±0,100	±0,004	20.7	•	•	•	•	•	•	•	•	•				
27723802	1D	0-3800	0-50					24.5	•	•	•	•	•	•	•	•	•				
27723800	2D			0,01		±0,160	±0,006	25	•	•	•	•	•	•	•	•	•	Folders / 2000 val	Long range / HID	USB HID / Update	Touchscreen 2.4"
<b>2D LASER MACROPROFILE STAND</b>																					
27720907	2D	0-900	0-8		0.002	±0,030		7.0	•	•	•	•	•	•	•	•	•				
27720908	2D		0-40		0,01			7.2	•	•	•	•	•	•	•	•	•				
27721807	2D	0-1800	0-8		0.002			11.5	•	•	•	•	•	•	•	•	•				
27721808	2D		0-40	0,01	0,01	±0,060		11.7	•	•	•	•	•	•	•	•	•				
27722807	2D	0-2800	0-8		0.002			20.5	•	•	•	•	•	•	•	•	•				
27722808	2D		0-40		0,01	±0,100		20.7	•	•	•	•	•	•	•	•	•				
27723807	2D	0-3800	0-8		0.002			24.5	•	•	•	•	•	•	•	•	•				
27723808	2D		0-40		0,01	±0,160		25	•	•	•	•	•	•	•	•	•	Folders / 2000 val	Long range / HID	USB HID / Update	Touchscreen 2.4"

# PIPE STRAIGHTNESS CONTROL COMPUTERIZED STAND



0,1µm

PAT.UA521681  
PAT.UA140992

Item No	Axis	Range		Resolution	Accuracy		Weight	Preset	Go/NoGo	Max/Min	Formula	Timer	Temp comp	Linear corr	Calibr date	Recharge	Memory	WIRELESS	USB	Display
		X	Z		X	Z														
		mm	mm		mm	mm														
27520900		0-900			±0,040	±0,002	10	•	•	•	•	•	•	•	•	•	•	•	•	•
27521800	2D	0-1800	0-12	0,0001	±0,080	±0,002	15	•	•	•	•	•	•	•	•	•	•	•	•	•
27522800		0-2800			±0,120	±0,002	35	•	•	•	•	•	•	•	•	•	•	•	•	•